BAUSCH & LOMB STEREOZOOM® MICROSCOPES

Catalog D-15

SERIES A. For opaque objects		
Model No.	Catalog No.	Suggested List Price
AFB-1	31-26-29-01	\$258.00
AFB-2	31-26-29-02	258.00
AVB-12	31-26-29-12	320.00
AVB-73	31-26-29-73	405.00
SERIES	B. For opaque and transpa	arent objects
BFB-1	31-26-30-01	\$294.00
BFB-2	31-26-30-02	294.00
BVB-12	31-26-30-12	356.00
BVB-73	31-26-30-73	441.00
S	ERIES K. For opaque obj	jects
KFB-1	31-26-39-01	\$320.00
KFB-2	31-26-39-02	320.00
KVB-12	31-26-39-12	382.00
KVB-73	31-26-39-73	467.00
SE	RIES KT. For opaque ob	jects
KTFB-1	31-26-37-01	\$331.00
KTFB-2	31-26-37-02	331.00
KTVB-12	31-26-37-12	393.00
KTVB-73	31-26-37-73	478.00
Si	ERIES S. For opaque obje	ects
SFB-1	31-26-40-01	\$320.00
SFB-2	31-26-40-02	320.00
SVB-12	31-26-40-12	382.00

SVB-73

31-26-40-73

467.00

SERIES SK. For opaque objects

Model No.	Catalog No.	Suggested List Price
SKFB-1	31-26-41-01	\$549.00
SKFB-2	31-26-41-02	549.00
SKVB-12	31-26-41-12	611.00
SKVB-73	31-26-41-73	696.00

DEPTH MEASURING STEREOMICROSCOPE. For opaque objects
ADM-2 31-26-44-02 \$400.00

STEREOZOOM TRAINING MICROSCOPE SET-UPS. For opaque and transparent objects

Description	Suggested List Price
Fixed Power, 5×, for opaque objects only. Consisting of Models- F (31-26-39-02) and AFB-1 (31-26-29-01); 31-26-18, 0.5× Suj mentary Lens Attachment; 31-34-83, Vertical Illuminator	nnle-
Fixed Power, 5×, for both opaque and transparent objects. Sam above, except with Model BFB-1 (31-26-30-01) in place of the AFE	ne as 3-1 680.0 0
Variable Power, 10 × thru 20 ×, for opaque objects only. Consistin Models KVB-12 (31-26-39-12) and AVB-12 (31-26-29-12); 31-20 0.5 × Supplementary Lens Attachment; 31-34-83, Vertical Illumin	6-18
Variable Power, 10× thru 20×, for both opaque and transpa objects. Same as next above, except with Model BVB-12 (31-26-30 in place of the AVB-12.	1.12\
Variable Power, 7× thru 30×, for opaque objects only. Consistin Models KVB-73 (31-26-39-73) and AVB-73 (31-26-29-73); 31-26-0.5× Supplementary Lens Attachment; 31-34-83, Vertical Illumin	ng of
Variable Power, 7× thru 30×, for both opaque and transparent obje Same as next above, except with Model BVB-73 (31-26-30-73 place of the AVB-73.	in (

ILLUMINATORS

Cat. No.		Suggester List Price
31-33-53	Nicholas Illuminator with 6.5-v., 2.75-amp. prefocus lamp, lamp housing, fixed focus condenser in friction ring clamp on adjustable link arm removable from base by knurled screw; adjustable intensity transformer base with switch, cord and plug for 115-v., 60 cycle A.C	15-02-11
31-33-56	Nicholas Illuminator, same as No. 31-33-53 except with fixed intensity transformer base	
31-33-36	Fluorescent Illuminator with two 4 watt daylight tubes, opalescent diffusor and switch; adjustable link arm detachable from illuminator housing or base by knurled screws; with base, cord and plug for 115-v., 60 cycle A.C.	
31-33-24-01	Reflector Illuminator with 30-w., 120-v. lamp, reflector, and adjustable link arm detachable from base by knurled screw; with base, cord, switch and plug for 115-v.	
31-34-83	Vertical Illuminator with reflector and locking device for orientation; in threaded mount to attach to stereomicroscope Power Pod; without light source	35.00
31-33-01	Micro-Lite with 60-w., 120-v. lamp, condenser and blue filter; ball and socket joint for inclination adjustment; with base, cord, switch and plug for 115-v	13.00

ACCESSORIES AND INTERCHANGEABLE PARTS

Su Description Li	ggested st Price
ACCESSORIES-EYEPIECE DISCS AND STAGE MICRON	METERS
Micrometer Disc, each least division value of 0.001" at	\$ 9.00
Micrometer Disc, each least division value of 0.002" at 2×	9.00
Micrometer Disc, each least division value of 0.005" at 1×	9.00
	9.00
	8.00
Cross Line Disc, 21mm dia	9.00
Glass Stage Micrometer, ruled 0.005" divisions	18.00
Glass Stage Micrometer, ruled to 0.001"	25.00
Glass Stage Micrometer, ruled to 0.1mm and 0.01mm	25.00
TRANS-ILLUMINATION BASE	
Attachable Base for series A StereoZoom Microscopes, for below-stage illumination of transparent objects; with illuminator part concave mirror flat diffusing reflector.	
mirror controls and clear glass plate	\$ 38.50
INTERCHANCEARIE DOWER DORS	PL CO
	155.0
graduated in 0.1×	217.0
0.7× thru 3× StereoZoom Variable Power Pod, knob dial graduated in 0.1×	302.0
YE RELIEF WIDE FIELD EYEPIECES, PAIRED, BALCOT	ED
10×, 0.870" eye relief, with eye guards, per pair	\$ 40.0
15 x 0.440" eye relief, with eye guards, per pair	40.0
15×, 0.440" eye relief, with eye guards, per pair 20×, 0.401" eye relief, with eye guards, per pair	
20×, 0.401" eye relief, with eye guards, per pair EYE GUARDS	40.00
20×, 0.401" eye relief, with eye guards, per pair	40.0 \$.4
$20 imes$, 0.401^{ν} eye relief, with eye guards, per pair	\$.4
EYE GUARDS For 10 × wide field eyepieces, each For 15 × and 20 × wide field eyepieces, each	\$.4
$20 imes$, 0.401^{ν} eye relief, with eye guards, per pair	\$.4
EYE GUARDS For 10 × wide field eyepieces, each For 15 × and 20 × wide field eyepieces, each	\$.4
	ACCESSORIES—EYEPIECE DISCS AND STAGE MICRON Micrometer Disc, each least division value of 0.001" at 3× Power Pod magnification

Catalog No.		uggested List Price
	STANDS A PRINCIPAL OF THE PRINCIPAL OF T	
31-26-65	Stand without arm; with lower rack and pinion; with fibre composition baseboard, 12" x 16". For series KT	\$ 76.00
31-26-88	Stand, with arm, for Series A and B	60.50
31-26-95	Stand, without arm, for Series K	
31-26-96	Stand, with collar clamp, without arm for Series S	65.00
31-26-97	Stand, without arm, for Series SK	280.0
- 00.	INTERCHANGEABLE ARMS	4
31-26-90	Rotatable Arm, allowing 630° rotation of Power Pod. For use on Series K, KT, S and SK models	\$ 74.0
31-26-59	Stationary Arm, for 180° reversal of Power Pod; upper rack and pinion and swivel joint; port for Nicholas Illuminator. Standard on series KT, K, and S and optional for SK.	
60.	STAGE PLATES FOR STEREOMICROSCOPES	8
31-26-86	Clear Glass Stage Plate for use on Series A and B	\$ 2.5
31-26-87	Opaque Contrast Plate, black on one side, white on reverse side, for use on series A and B	
312688-128	Stage Clip, large size, each	4
	CASES FOR STEREOZOOM MICROSCOPES	
31-40-11	Horizontal storage and carrying case, two-tone gray leath erette, with brackets for stage plate and pair of eye pieces; with handle, lock and key for Series B	•
31-40-11-12	Storage Case same as 31-40-11 above except for Series A	29.0
0.0	REPLACEMENT ILLUMINATOR LAMPS	18
31-31-79	Bulb, 6.5-v., 2.75-amp., for Nicholas Illuminator	\$ 1.1
31-31-03	Daylight Tube, 4-w., for Fluorescent Illuminator	
31-31-87	Bulb, 30-w., 120-v., for Reflector Illuminator	. 1.1
71-71-13	Daylight Bulb, 60-w., 120-v., for Micro-Lite Illuminato	

DESIGN CHANGES—Bausch & Lomb reserves the right to make changes in instrument design in accordance with scientific progress, and to supply apparatus resultingly different from that described or illustrated in its literature.

CATALOG NUMBERS—When ordering, be sure to give catalog number and name of item.

FINANCIAL STANDING—To avoid a delay, a purchaser with whom Bausch & Lomb has not previously transacted business should accompany his first order with commercial references

TRANSPORTATION CHARGES—Unless otherwise stated on a B&L quotation, all consumer purchases, except repairs, will be shipped transportation charges prepaid to any point within Continental United States of America. Other-than-consumer purchases, all repairs, and goods for delivery outside the above specified area will be shipped f.o.b. Rochester, N. Y., U.S.A. The shipping charges on products sent on memorandum are not prepaid. There is no charge for packing unless otherwise stated. Products made on special order cannot be forwarded C, O. D.

BAUSCH & LOMB INCORPORATED Rochester, New York, U.S.A. 14602